

## DEVIpipeline™ 10 (DPH-10) (B)

The DEVIpipeline™ 10 w/plug is a self-limiting heating cable that is mainly used for frost protection of pipes.

The self-limiting capability of the cable ensures that the output of the cable increase or decrease according to ambient temperature.

The heating cables can be installed inside or outside pipes. The product range: drum cable, cable with cold lead without mains plug and cable with cold lead with an EU Schuko mains plug.



### Benefits:

- Cut to length on site
- Ready made lengths
- Can be installed inside pipes

### Standard compliance:

- IEC 60335-1:2012
- IEC 62233:2008

### Approvals:



Type	Value
Operation voltage	230 V~
Output (min-max)	10 W/m @ 10 °C (8,5-13,5 W/m @ 10 °C)
Max. permissible use temperature, powered	65 °C
Max. permissible use temperature, unpowered	85 °C
Minimum use temperature	- 30 °C
Heating cable dimensions	7,7 mm x 5,3 mm
Outer sheath	Blue, TPE
Minimum Screen Coverage	100% aluminium foil
Maximum resistance protective braid	18,2 Ω/Km
Bending Ø, min.	50 mm (Ø to the inside of the cable)
Cold tail with plug	1,5 m, 3 x 1 mm <sup>2</sup> , Schuko plug
Max. installation length on a pipe with 10 A circuit breaker with C-characteristic	100 m (60 m inside the water pipe) 96 m 77 m

### Types

Item no.	Type	Length	Min-max length per drum	Number of length allowed on drum, max	Output @ 10 °C	EAN no.
98300016	DEVIpipeline™ 10	Drum, 100 m	100 m	1	10 W/m	5703466217771
98300015	DEVIpipeline™ 10	Drum, 270 m	270-330 m	1	10 W/m	5703466217764
98300017	DEVIpipeline™ 10	Drum, 900 m	900-1100 m	2, between 100 & 1100 m	10 W/m	5703466217788
140F0711	DEVIpipeline™ 10 no plug	2 m	-	-	20 W	5703466218143
140F0712	DEVIpipeline™ 10 no plug	4 m	-	-	40 W	5703466218150
140F0713	DEVIpipeline™ 10 no plug	6 m	-	-	60 W	5703466218167
140F0714	DEVIpipeline™ 10 no plug	8 m	-	-	80 W	5703466218174
140F0715	DEVIpipeline™ 10 no plug	10 m	-	-	100 W	5703466218181
140F0716	DEVIpipeline™ 10 no plug	12 m	-	-	120 W	5703466218198
140F0717	DEVIpipeline™ 10 no plug	14 m	-	-	140 W	5703466218204
140F0718	DEVIpipeline™ 10 no plug	16 m	-	-	160 W	5703466218211
140F0719	DEVIpipeline™ 10 no plug	19 m	-	-	190 W	5703466218228
140F0720	DEVIpipeline™ 10 no plug	22 m	-	-	220 W	5703466218235
140F0721	DEVIpipeline™ 10 no plug	25 m	-	-	250 W	5703466218242
98300071	DEVIpipeline™ 10 with plug	2 m	-	-	20 W	5703466217924
98300072	DEVIpipeline™ 10 with plug	4 m	-	-	40 W	5703466217931
98300073	DEVIpipeline™ 10 with plug	6 m	-	-	60 W	5703466217948
98300074	DEVIpipeline™ 10 with plug	8 m	-	-	80 W	5703466217955
98300075	DEVIpipeline™ 10 with plug	10 m	-	-	100 W	5703466217962
98300076	DEVIpipeline™ 10 with plug	12 m	-	-	120 W	5703466217979
98300077	DEVIpipeline™ 10 with plug	14 m	-	-	140 W	5703466217986
98300078	DEVIpipeline™ 10 with plug	16 m	-	-	160 W	5703466217993
98300079	DEVIpipeline™ 10 with plug	19 m	-	-	190 W	5703466218006
98300080	DEVIpipeline™ 10 with plug	22 m	-	-	220 W	5703466218013
98300081	DEVIpipeline™ 10 with plug	25 m	-	-	250 W	5703466218020
19805366	¾" + 1" Pipe fitting for DEVIpipeline™ 10 (DPH-10)			With rubber conic sliced sleeve, oval hole		5703435041697