









## DEVIreg™ 132

The DEVIreg™ 132 is a simple electronic thermostat to be installed directly on the wall, using a room sensor to control the room temperature and a floor sensor (wire) to limit the maximum floor temperature.

The thermostat has a dial for adjusting the temperature, with a scale from 5° C - 35° C and an LED indicating the current mode (heating, standby or fault).

Benefits:	Type	Value
<ul style="list-style-type: none"> <li>Double pole safety breaker</li> <li>Sensor failure monitoring</li> <li>LED indication</li> <li>Room and floor sensors</li> <li>Frost protection</li> </ul> <p><b>Standard compliance:</b></p> <ul style="list-style-type: none"> <li>EN/IEC 60730-1 (general) and EN/IEC 60730-2-9 (thermostat)</li> </ul> <p><b>Approvals:</b></p> <div style="display: flex; align-items: center; gap: 10px;">     </div>	Operation voltage	220 V- 240V~ 50/60 Hz
	Standby power consumption	Max. 5 W
	Relay: Resistive load Inductive load	Max 16A / 3680W @ 230V Cos Φ = 0.3 max. 1A
	Sensing unit	NTC 15 kOhm at 25° C
	Hysteresis	± 0.2° C
	Ambient temperature	0° C. to +30° C
	Frost protection	5° C - 
	Temperature range	5° C - 35° C room temperature 20° C - 50° C floor temperature limiter - default 35° C
	Cable specification max	1 x 4 mm <sup>2</sup> or 2 x 2,5 mm <sup>2</sup>
	Ball pressure test temperature	75° C
Pollution degree	2 (domestic use)	
Controller type	1 C	
Storage temperature	-20° C to +65° C	
IP class	30	
Protection class	Class II - 	
Dimensions (H/W/D)	82 mm x 82 mm x 36 mm	
Weight	90 g	

### Types

Item no.	Product name	Type	EAN no.
140F1011	DEVIreg™ 132	With floor sensor and room sensor	5703466208960