



DEVIsnow™ Drum Goods (DTCE) NEW


DEVIsnow™ heating cable on drum is an extremely high-quality, 360° fully screened twin conductor cable with a tough black PVC outer sheath (UV stable). Its round profile and robust construction ensures a fast, simple and safe installation on roofs, in gutters, down drain pipes and on the ground.

To ensure a long life-time, all cables are minutely inspected including tests for Ohmic resistance, high voltage and material controls to ensure the quality. This means that we are proud to supply our extended DEVIwarranty™.

DEVIsnow™ can be customized for the specific project, depending on voltage, required output, length of heating cable and length of cold leads.



Note: It is the full responsibility of the installer/designer to use proper cold lead dimensioned for the purpose and assembly sets that establish sufficient mechanical strength, flammability resistance and water tightness - and to design the heating unit with correct output for the specific application to avoid overheating of the cable or building materials.

Benefits: <ul style="list-style-type: none"> • Fast and easy to install • Multiple outdoor applications • Safe and robust • Long life-time • Maximum protection • UV stable Standard compliance: <ul style="list-style-type: none"> • IEC60800:2009 Approvals: 	Type	Value	
	Operation voltage, max		$U_o/U = 300/500 V\sim$
	Construction		Twin conductor with 360° screening
	Output, max		30 W/m
	Max. permissible use temperature, powered		60 °C
	Max. permissible use temperature, unpowered		90 °C
	Cable diameter		7 mm
	Deformation strength		>1500 N
	Pulling strength		>300 N
	Conductor insulation		FEP
	Outer sheath		UV protected PVC
	Screen		0,5 mm ² Cu, 100% Alu-foil
	Min. installation temperature		-5 °C
	Bending Ø, min.		50 mm
IP Class		IPX7	

Types

Item no.	Resistance	EAN no.
84805400	9,36 Ω/m	5703466146248
84805403	4,19 Ω/m	5703466146255
84805406	2,368 Ω/m	5703466146262
84805409	1,519 Ω/m	5703466146279
84805412	1,057 Ω/m	5703466146286
84805415	0,735 Ω/m	5703466146293
84805418	0,567 Ω/m	5703466146309
84805421	0,451 Ω/m	5703466146316
84805424	0,367 Ω/m	5703466146323
84805427	0,257 Ω/m	5703466146330
84805430	0,19 Ω/m	5703466146347
84805433	0,146 Ω/m	5703466146354
84805436	0,115 Ω/m	5703466146361
84805439	0,092 Ω/m	5703466146378
84805442	0,07 Ω/m	5703466146385
84805445	0,055 Ω/m	5703466146392

Accessories

Item no.	Name	Description	EAN no.
18055249	DEVICrimp™ for DEVIsnow (DTCE)	Connection kit for DEVIsnow™ (DTCE)	5703466199251
18055350	DEVICrimp™ ass/repair kit 2-cond. Cs2a/cs2b	Connection kit for twin-conductor heating cable	5703466003381